




SciAps Z-902 Carbon Analyzer Specifications

In-use globally



- Third-party inspection companies
- Pipeline inspection companies
- Chemical plants
- Refineries
- Manufacturing
- Shipbuilders
- Steel makers
- Scrap processing

The world's first handheld analyzer to deliver carbon content just got better. SciAps Z-902 Carbon is the key to rock-solid, in-field analysis for alloys. Confirm alloy type and grade 300 series stainless into L, H, and S series. Determine carbon equivalents for welding. Perform material verification pre- and post-fabrication.



A new standard for NDT/PMI

Identification of stainless steels and low alloy steels, including carbon analysis down to 70 ppm and instant CE (carbon equivalence) calculations using our uniquely powerful laser, onboard argon purge and high-resolution spectrometer.

- **On-board argon** delivers results for pennies per test.
- **Powerful laser** delivers 5-6 mJ/pulse on the sample, with a 50 Hz repetition rate. High energy and high repetition rate mean a clean burn.
- **Laser raster** can rapid-sample multiple locations in one test for fuller data.
- **Analysis averaging** available for multi-shot averaging and data rejection.
- **Sample alignment** micro-camera and LED Spotlight focus just where you want.

190 nm – 420 nm spectrometer

Includes a dedicated spectrometer for superior resolution in the 190 – 230 nm range

For more information, or to schedule a demonstration:

SciAps.com
+1 339.927.9455

SciAps

True portability

Only 4.35 lbs (1.97 kg) with battery and a narrow profile for accessing the tightest spaces; an aerospace-grade aluminum body for improved performance in high ambient temperatures; and a re-designed, Android-based user-interface all make this system the most usable platform on the market. Wifi and Bluetooth with GPS capability to print, email, and connect to virtually any information management system for efficient, real-time test data and reporting.



SciAps Z-902 Carbon Analyzer Specifications



SciAps Cloud Services

You use XRF for metals in alloys, because it's the best technology for most PMI. But what about carbon? Two reports? Not with SciAps Cloud. Get efficient real-time results, data merge and management, and full-featured report generation for XRF and LIBS.

Weight	4.35 lbs. (1.97 kg) with battery
Dimensions	10.75 x 2.875 x 8.625 inches
Display	2.7" high-brightness, color touchscreen, readable in all lighting conditions. Rear-facing display for easy results viewing.
Power	On-board rechargeable Li-ion battery, rechargeable inside device or with external charger, AC power.
Processing Electronics	ARM Quad Cortex -A53 1.2 GHz Memory: 2 GB LPDDR3, 16 GB eMMC
Data Storage	Results storage: 32 GB SD
Connectivity	Built on Google's Android platform for real-time data exporting, including built-in WiFi (IEEE 802.11b/g/h), Bluetooth (BR/EDR+BLE), GPS and USB-C to connect to virtually any information management system.
Sample Viewing	Integrated camera and laser target indicator for viewing sample before and during analysis for proper sample alignment. Includes second "macro camera" for scanning QR or barcodes and for photo-documentation and report generation.
Laser Raster	On-board Y stage for rastering laser to discrete locations for targeted analysis or averaging.
Atmosphere	SciAps proprietary Opti-Purge provides an inert argon environment, improving spectral signal-to-noise ratio and improving performance in the UV range.
Calibration Check	316 stainless steel standard for automated calibration and wavelength scale validation.
Drift Correction	On-board automated drift correction software with factory-provided or user-provided reference materials.
Grade Library	500+ grades, multi-library support, libraries may be added or edited.
Regulatory	CE, RoHS, USFDA registered. Class 3b laser. Sample sensor on board, allows for operation under Class 1 conditions, subject to local LSO approval.
Spectral Range	190 – 420 nm
Calibrations	Aluminum: Be, Mg, Al, Si, Ti, V, Cr, Mn, Fe, Ni, Cu, Zn, Zr, Pb, Bi, Ag, Sn Titanium Base: Al, Ti, V, Cr, Fe, Cu, Zr, Nb, Mo, Sn LAS Base: C, Al, Si, Ti, V, Cr, Mn, Fe, Cu, Ni, Nb, Mo, Pb Stainless Steels: C, Al, Si, Ti, V, Cr, Mn, Ni, Fe, Ni, Cu, Nb, Mo, W Nickel Base: Al, Si, Ti, Cr, Mn, Fe, Co, Ni, Cu, Nb, Mo, W Copper Base: Be, Al, Si, Cr, Mn, Fe, Ni, Cu, Zn, Ag, Sn, Pb, Bi Cobalt Base: Al, Si, Ti, Cr, Mn, Fe, Co, Ni, Cu, Nb, Mo, W Specialty Bases: Mg, V, Cr, Mn, Co, Zn, Zr, Nb, Mo, Ag, Sn, Hf, Ta, W, Re, Pb, Sn.
Security	Password protected; Multi-user support with configurable access settings

JUN2021

EndoMatrix (M) Sdn Bhd
No. 51-5, Block G, Dataran Prima, Jalan PJU 1/37,
47301 Petaling Jaya, Selangor Darul Ehsan, Malaysia.
Phone: 03-7803 1145 | Fax: 03-9101 4814
sales@endomatrix.com.my | www.endomatrix.com.my

SciAps Inc.
7 Constitution Way
Woburn, MA 01801
sales@sciaps.com
SciAps.com
+1 339.927.9455

 [YouTube.com/SciAps](https://www.youtube.com/SciAps)

SciAps