



SciAps X-505 Specifications

**Simply the best
handheld XRF
ever made**

- Fast on all alloys, including aluminums
- Optimized for sulfidic corrosion (low Si)
- Designed for residuals analysis, per API 751 and 5L specifications

The SciAps X Series sets a new performance standard for handheld XRF. It's the lightest, fastest, most articulate X-ray platform — 2.98 lbs. with battery — delivering small size, blazing speed and high precision in a perfectly balanced device. The X-505 was especially designed for NDT, PMI users who must access hard-to-reach test locations and welds. The X-505 also features a powerful, miniaturized X-ray tube designed to excel at measuring low atomic number elements Si, P, S, Mg and Al. This tube combined with highly optimal internal geometry yields fast, precise results on previously challenging applications like measuring silicon for sulfidic corrosion, and low magnesium in aluminum alloys.



Fast, precise tests with SciAps X-505

SciAps X-505 analyzes common alloys in 1 second or less. Alloys requiring longer test times or two-beam light-element analysis are readily measured by SciAps industry-specific testing apps. Tap the Alloy App for ultra-fast verification of any metal. Even aluminum grades that confound other X-ray guns — 3003/3004/3005, cast 356 and 357, and 2014/2024 — are easy for the X-505. Switch from the Alloy App to the Residuals App, for example, and the analyzer uses pre-set testing times to measure low concentrations of Cr, Ni, and Cu, then calculates its sum. Operators won't be adjusting test times in the field or generating unexceptional data due to insufficient testing times.

Connectivity and Android

The X Series is built on Google's Android platform for real-time data exporting. The user interface has the feel of a smartphone with results easily viewed on a vibrant display and reversible light/dark for all lighting conditions. **Built-in Wi-Fi, Bluetooth, GPS and USB** mean that users can print and email from the X and connect to virtually any information management system for efficient test data and reporting.



XRF & LIBS

Need carbon? Add LIBS in One Box.

For users who need to also measure carbon in steels, stainless and cast iron, SciAps manufactures the Z — the world's only handheld laser system (LIBS) capable of measuring carbon content low enough to separate L and H grade stainless. SciAps Z has achieved global acceptance with nearly 1,000 units delivered. The Z also analyzes beryllium, boron and lithium in alloys. Packaged together with shared accessories in the One Box, the X and Z provide optimal performance for virtually every alloy and element, and for less money than a comparable spark OES system.

For more information, or to
schedule a demonstration:

SciAps.com
+1 339.927.9455

SciAps



**Ultra fast,
precise, and
articulate XRF**

SciAps X-505 Handheld XRF Specifications

Weight	2.98 lbs. with battery
Dimensions	8.5" x 9.5" x 2.4"
Excitation Source	5 W X-ray tube. Typical: 40 kV, 200 uA Rh anode and 10kV, 200 uA for alloy testing, 50 kV, 200 uA Au anode for most other apps
Detector	20 mm ² silicon drift detector (active area), 140 eV resolution FWHM at 5.95 Mn K-alpha line
Available Apps	Alloy, Geochem (Mining), Empirical, Environmental apps. New apps are added regularly, please check with company or website.
X-ray Filtering	4 position filter wheel for beam optimization
Environmental Temperature Range	10F to 130F at 25% duty cycle
Analytical Range	32 elements standard, specific elements vary by app. Additional elements may be added upon user request. Precious metals app is 22 elements standard.
Processing Electronics and Host Processing	1.2GHz quad ARM Cortex A53 64/32-bit, RAM: 2GB LP-DDR3, Storage: 16 GB eMMC (storage)
Pulse Processor	12 bit with digitization rate of 80 MSPS 8K channel MCA USB 2.0 for high-speed data transfer to host processor. Digital filtering implemented in FPGA for high throughput pulse processing 20 nS - 24 uS peaking time.
Power	On-board rechargeable Li-ion battery, rechargeable inside device or with external charger, AC power, hot-swap capability (60 s max swap time)
Display	2.7-inch color capacitive touchscreen — 400 MHz Qualcomm Adreno 306 2D/3D graphics accelerator
Comms/Data Transfer	Wi-Fi, Bluetooth, USB connectivity to most devices, including SciAps Profile Builder PC software
Calibration	Fundamental parameters. For Geochem and Environmental Soil apps, users may also choose "Compton Normalization" method and/or use empirically derived calibrations.
Calibration Check	External 316 stainless check standard for calibration verification and energy scale validation
Grade Library	Standard library contains 500+ grades, no practical size limit. Multiple libraries supported, grades may be added on analyzer or via PC software package (ProfileBuilder)
Security	Password protected usage (user level) and internal settings (admin)
Regulatory	CE, RoHS, USFDA registered, Canada RED Act

OCT21

EndoMatrix (M) Sdn Bhd
No. 51-5, Block G, Dataran Prima, Jalan PJU 1/37,
47301 Petaling Jaya, Selangor Darul Ehsan, Malaysia.
Phone: 03-7803 1145 | Fax: 03-9101 4814
sales@endomatrix.com.my | www.endomatrix.com.my

SciAps Inc.
7 Constitution Way
Woburn, MA 01801
sales@sciaps.com
SciAps.com
+1 339.927.9455

 [YouTube.com/SciAps](https://www.youtube.com/SciAps)

SciAps